Pushing Performance
Since 1945

RJ45 - M12 x-code Cable Assy 15m PVC



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 932 3757 150
Specification	RJ45 - M12 x-code Cable Assy 15m PVC
HARTING eCatalogue	https://harting.com/09489323757150

Identification

Category	System cabling
Series	Circular connectors M12 RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Straight
Connector 2	HARTING RJ Industrial® Gigalink Straight
Type of cable	Copper cable (round)

Version

Cable length	15 m
Number of cores	8
Core structure	8x AWG 26/7
Coding	X-coding

Technical characteristics

Transmission characteristics	Cat. 6_A Class E_A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +70 °C

Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	776 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140266964
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com