Pushing Performance
Since 1945

ICC20_H_WMRF_BL



Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 3010
Specification	ICC20_H_WMRF_BL
HARTING eCatalogue	https://harting.com/19591203010

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight Front mounting / Rear mounting

Version

Size	20
Locking type	Bayonet locking
Details	Please order backshell or fixing nut separately.

Technical characteristics

Tightening torque	0.5 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP67 IPX9

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	EPDM
Colour (seal)	Black
RoHS	compliant

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
PFAS	No
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	no requirements (flammable mass < 10g)

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	51.8 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140491137
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com