This product is not orderable anymore. Please contact your local distribution partner.

Pushing Performance
Since 1945

M12 A-cod 3-pol st/- m/- PVC 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 100 0333 010
Specification	M12 A-cod 3-pol st/- m/- PVC 1.0m

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Straight Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	3
Core structure	3x AWG 22/7
Shielding	Shielded
Coding	A-coding

Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-40 ... +80 °C
Cable diameter	5 mm ± 0.15 mm

Material properties

Material (cable)	PVC

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

Colour (cable)	Grey

Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140809710
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com