Product data sheet
21 40 120 0552 100
M12 A-cod 5-pol an/- m/- PUR 10.0m
This product is not orderable anymore. Please contact your local distribution partner.

Pushing Performance
Since 1945

M12 A-cod 5-pol an/- m/- PUR 10.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 120 0552 100
Specification	M12 A-cod 5-pol an/- m/- PUR 10.0m

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Angled Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	5
Core structure	5x 0.34 mm²
Shielding	Shielded
Coding	A-coding

Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-50 ... +80 °C unmoved -30 ... +80 °C moved
Cable diameter	4.7 mm ± 0.2 mm
Minimum bending radius	5x Cable diameter (singular bending) 10x Cable diameter (repeated bending)

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black

Commercial data

Packaging size	1
Net weight	400 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140807778
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com