Product data sheet
21 40 300 0446 100
M12 D-cod 4-pol st/- m/- PVC 10.0m
This product is not orderable anymore. Please contact your local distribution partner.

Pushing Performance
Since 1945

M12 D-cod 4-pol st/- m/- PVC 10.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 300 0446 100
Specification	M12 D-cod 4-pol st/- m/- PVC 10.0m

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding Male Straight Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7
Shielding	Shielded
Coding	D-coding

Technical characteristics

Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C unmoved -20 ... +60 °C moved
Cable diameter	6.5 mm ± 0.2 mm

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Minimum bending radius	3x Cable diameter (singular bending) 5x Cable diameter (repeated bending)

Material properties

Material (cable)	PVC
Colour (cable)	Green

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock

Commercial data

Packaging size	1
Net weight	714.3 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140807143
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com