Pushing Performance
Since 1945

InduCom 15p 2T-entry kn-screw 4-40 w/o



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 001 0116 010
Specification	InduCom 15p 2T-entry kn-screw 4-40 w/o
HARTING eCatalogue	https://harting.com/61030010116010

Identification

Category	Hoods / Housings
Series	D-Sub
Identification	InduCom
Type of hood/housing	Shell housing
Description of hood/housing	Without internal earth

Version

Size	D-Sub 2
Version	Top entry
Number of cable entries	2
Cable entry	2x
Strain relief	An additional InduCom cable clamp or a crimp flange - ferrule combination is available dependant on the use of the cable.
Locking type	Knurled screw Thread 4-40 UNC
ground connection	Without internal grounding block
2 parts	Yes
Separable	Yes
Details	Part number includes one dummy plug

Technical characteristics

Tightening torque	0.4 Nm cover screw 0.4 Nm Locking screw
Limiting temperature	-55 ... +125 °C

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP30

Material properties

Material (hood/housing)	Zinc die-cast
Material (screw)	Steel, nickel plated
Length	51.9 mm
Width	39.5 mm
Height	14.8 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	70.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140222656
eCl@ss	27440213 D-Sub hood
ETIM	EC001133
UNSPSC 24.0	39121416

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com