Pushing Performance
Since 1945

InduCom 37p T&S-entry hexscrew 4-40 w/o




Image is for illustration purposes only. Please refer to product description.

Part number	61 03 001 2018 010
Specification	InduCom 37p T&S-entry hexscrew 4-40 w/o
HARTING eCatalogue	https://harting.com/61030012018010

Identification

Category	Hoods / Housings
Series	D-Sub
Identification	InduCom
Type of hood/housing	Shell housing
Description of hood/housing	Without internal earth

Version

Size	D-Sub 4
Version	Top/side entry
Number of cable entries	3
Cable entry	3x
Strain relief	An additional InduCom cable clamp or a crimp flange - ferrule combination is available dependant on the use of the cable.
Locking type	Hexagonal screw with captive washer Thread 4-40 UNC
ground connection	Without internal grounding block
2 parts	Yes
Separable	Yes
Details	Part number includes two dummy plugs

Technical characteristics

Tightening torque	0.4 Nm cover screw 0.4 Nm Locking screw
Ambient temperature	-55 ... +125 °C

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP30

Material properties

Material (hood/housing)	Zinc die-cast
Material (screw)	Steel, nickel plated
Length	42.4 mm
Width	69.5 mm
Height	14.8 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	23 g
Country of origin	China
GTIN	5713140221758
eCl@ss	27440213 D-Sub hood
ETIM	EC001133
UNSPSC 24.0	39121416

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com