Pushing Performance
Since 1945

Pwr Q4/2 female angled TC ER 4G6qmm 2m



Image is for illustration purposes only. Please refer to product description.

Part number	61 04 201 2740 L020
Specification	Pwr Q4/2 female angled TC ER 4G6qmm 2m
HARTING eCatalogue	https://harting.com/61042012740L020

Identification

Element	Energy supply
Specification	Pre-assembled on one side
Connector 1	Han-Compact® Hood Side entry Han® Q 4/2 Female
Type of cable	Copper cable (round)

Version

Cable length	2 m
Core structure	4G 6 mm²
PE contact	Yes
Field of application	Power cables

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140275645
eCl@ss	27060327 Assembled power cable
ETIM	EC002587
UNSPSC 24.0	43211600

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com