Pushing Performance
Since 1945

Pwr Q4/2 f/m ang./ang. TC ER 4G6qmm 2m



Image is for illustration purposes only. Please refer to product description.

Part number	61 04 202 2952 L020
Specification	Pwr Q4/2 f/m ang./ang. TC ER 4G6qmm 2m
HARTING eCatalogue	https://harting.com/61042022952L020

Identification

Element	Energy supply
Specification	Pre-assembled differently on both sides
Connector 1	Han-Compact® Hood Side entry Han® Q 4/2 Male
Connector 2	Han-Compact® Hood Side entry Han® Q 4/2 Female
Type of cable	Copper cable (round)

Version

Cable length	2 m
Core structure	4G 6 mm²
Number of contacts	6
PE contact	Yes
Field of application	Power cables

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140275805
eCl@ss	27060327 Assembled power cable
ETIM	EC002587
UNSPSC 24.0	43211600

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com