Pushing Performance
Since 1945

Han-Mod_AC_Cap_f.CableLug_400A



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 3456
Specification	Han-Mod_AC_Cap_f.CableLug_400A
HARTING eCatalogue	https://harting.com/97000003456

Identification

Category	Accessories
Series	Han-Modular®
Type of accessory	Protection cover
Description of the accessory	Han® 400 A module

Version

Details	The vibration and shock resistance can only be met if the cables are fixed at an appropriate distance. Instructions for the spacing of strain relief can be found in the document in eCatalogue under the section Instructions.

Technical characteristics

Rated current	400 A
Rated voltage	1,000 V
Rated voltage	1,000 V AC 1,500 V DC
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	$>10^{10}$ Ω
Limiting temperature	-40 ... +125 °C

Material properties

Material (hood/housing)	Polycarbonate (PC)
RoHS	compliant
ELV status	compliant

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	1
Net weight	26 g
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com