


this crimp contact should be processed with:


locator 09 99 000 0638

hand crimping tool 09 99 000 0509



surface specification

pl	Ni [µm]	NiP (µm) (P=10,5-13%)	ΣNi+NiP [µm]	Au [µm]
1	min. 1,5	min. 1,5	max. 5,5	min. 0,15



All Dimensions in mm  
Original Size DIN A4

Scale  
10:1

Free size tol.

Ref.

Sub.



All rights reserved

Department EL PD

Created by  
HASSE

Inspected by  
FRIESENH

Standardisation

Date  
2021-08-30

State  
Final Release

Title  
M12-P-CON-1.5-AWG20/0.5 mm<sup>2</sup>-F

Doc-Key / ECM-Nr.  
100752426/UGD/001/C  
500000201785

HARTING  
D-32339 Espelkamp

Type  
TB

Number  
21011009964

Rev. C Page  
1/1