

Number of contacts

3+

10 A 230/400 V 4 kV 3

Han A

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han A[®], Hood, HARAX[®] connection technology, Top entry, IP65, IP67</p> <p>Contact surface: Silver plated</p>	0.75 ... 1.5	09 20 003 0440	09 20 003 0445	
<p>Han A[®], Cable to cable housing, HARAX[®] connection technology, Top entry, IP65, IP67</p> <p>Contact surface: Silver plated</p>	1 ... 1.5		09 20 003 0745	