Han® M hoods/housings



Features

- · Hoods/housings for rough environments
- Metal hoods and housings with excellent corrosion resistance
- Corrosion resistance ASTM B117-09 (500 h)
- · Locking lever made of high-quality stainless steel

Technical characteristics

Limiting temperature -40 ... +125 °C Degree of protection acc. to IEC IP65, IP66, IP67

60529

Type rating acc. to UL 50 / UL 50E 4, 4X, 12

Material (hood/housing) Aluminium die-cast Surface (hood/housing) Powder-coated Colour (hood/housing) RAL 9005 (jet black)

 FPM Material (seal)

Material (locking) Stainless steel, Polycarbonate

RAL 7037 (dust grey)

Colour (locking) Polyamide (PA), Stainless steel Material (accessories)

Material flammability class acc.

to UL 94 (locking levers)

RoHS

compliant

Specifications and approvals

UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 DNV GL

 ϵ