## Han® Easy Hood hoods/housings



**Features** 

· Hoods/housings for industrial applications

## Technical characteristics

-40 ... +125 °C Limiting temperature

Degree of protection acc. to IEC IP54 60529

Type rating acc. to UL 50 / UL 50E 4, 4X, 12

Material (hood/housing) Aluminium die-cast Surface (hood/housing) Powder-coated Colour (hood/housing) RAL 7037 (dust grey)

Material (seal)

Material (locking) Polycarbonate (PC), Stainless

Colour (locking) RAL 7037 (dust grey)

RoHS compliant

## Specifications and approvals

DNV GL

Han