





Modular

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																																							
		Male	Female																																								
Han E®, Crimp contact, Contact surface: Silver plated 	0.14 ... 0.37		09 33 000 6227	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th colspan="2">Identification</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup></td> <td>AWG 26-22</td> <td>no groove</td> </tr> <tr> <td>0.5 mm<sup>2</sup></td> <td>AWG 20</td> <td>no groove</td> </tr> <tr> <td>0.75 mm<sup>2</sup></td> <td>AWG 18</td> <td>1 groove*</td> </tr> <tr> <td>1 mm<sup>2</sup></td> <td>AWG 18</td> <td>1 groove</td> </tr> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>2 groove</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>3 groove</td> </tr> <tr> <td>3 mm<sup>2</sup></td> <td>AWG 12</td> <td>wide groove</td> </tr> <tr> <td>4 mm<sup>2</sup></td> <td>AWG 12</td> <td>no groove</td> </tr> </tbody> </table> <p>* on the back crimp collar</p> <p>Stripping length 7.5 mm</p>  <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.75-1 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.45 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>1.75 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>2.25 mm</td> </tr> </tbody> </table>	Conductor cross-section	Identification		0.14-0.37 mm <sup>2</sup>	AWG 26-22	no groove	0.5 mm <sup>2</sup>	AWG 20	no groove	0.75 mm <sup>2</sup>	AWG 18	1 groove*	1 mm <sup>2</sup>	AWG 18	1 groove	1.5 mm <sup>2</sup>	AWG 16	2 groove	2.5 mm <sup>2</sup>	AWG 14	3 groove	3 mm <sup>2</sup>	AWG 12	wide groove	4 mm <sup>2</sup>	AWG 12	no groove	Conductor cross-section	∅	Stripping length	0.75-1 mm <sup>2</sup>	AWG 18	1.45 mm	1.5 mm <sup>2</sup>	AWG 16	1.75 mm	2.5 mm <sup>2</sup>	AWG 14	2.25 mm
	Conductor cross-section	Identification																																									
	0.14-0.37 mm <sup>2</sup>	AWG 26-22	no groove																																								
	0.5 mm <sup>2</sup>	AWG 20	no groove																																								
	0.75 mm <sup>2</sup>	AWG 18	1 groove*																																								
	1 mm <sup>2</sup>	AWG 18	1 groove																																								
	1.5 mm <sup>2</sup>	AWG 16	2 groove																																								
	2.5 mm <sup>2</sup>	AWG 14	3 groove																																								
	3 mm <sup>2</sup>	AWG 12	wide groove																																								
	4 mm <sup>2</sup>	AWG 12	no groove																																								
Conductor cross-section	∅	Stripping length																																									
0.75-1 mm <sup>2</sup>	AWG 18	1.45 mm																																									
1.5 mm <sup>2</sup>	AWG 16	1.75 mm																																									
2.5 mm <sup>2</sup>	AWG 14	2.25 mm																																									
0.5		09 33 000 6220																																									
0.75		09 33 000 6214																																									
1		09 33 000 6205																																									
1.5		09 33 000 6204																																									
2.5		09 33 000 6202																																									
3		09 33 000 6206																																									
4		09 33 000 6207																																									
Han E®, Crimp contact, Relay contact, Contact surface: Silver plated 	0.75 ... 1	09 33 000 6109																																									
	1.5	09 33 000 6110																																									
	2.5	09 33 000 6111																																									