## Modified contact arrangement



Han D

| Series Han DDD®   |   | Contact arrangement view from termination side  20 ⋅ ⊕  40 ⋅ ⊕        |  |
|---|---|---|--|
| Rated current<br>Rated voltage<br>Rated impulse voltage<br>Pollution degree | 10 A 400 V 6 kV 3<br>10 A<br>400 V<br>6 kV<br>3 | M F   |  |
| Rated current Rated voltage Rated impulse voltage Pollution degree          | 10 A 500 V 6 kV 3<br>10 A<br>500 V<br>6 kV<br>3 | • Working contact • Without contact M - Male insert F - Female insert |  |
|   |   |   |  |
|   |   |   |  |

Han 02 .