






Number of contacts

# 36

10 A 400 V 6 kV 3

Han  
HMC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																												
		Male	Female																													
<p>Han-Modular<sup>®</sup>, Han DD<sup>®</sup> module, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	0.14 ... 2.5	09 14 036 3002	09 14 036 3102	 <p>Contact arrangement (view from termination side)</p>																												
<p>Han D<sup>®</sup> HMC, Crimp contact, Contact surface: HMC gold plated</p> 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5	09 15 200 6124 09 15 200 6123 09 15 200 6125 09 15 200 6122 09 15 200 6121 09 15 200 6126	09 15 200 6224 09 15 200 6223 09 15 200 6225 09 15 200 6222 09 15 200 6221 09 15 200 6226	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>AWG</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup></td> <td>AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup></td> <td>AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section	AWG	Ø	Stripping length	0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm
Conductor cross-section	AWG	Ø	Stripping length																													
0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm																													
0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm																													
0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm																													
1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm																													
1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm																													
2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm																													
<p>Han D<sup>®</sup>, Han DD<sup>®</sup>, Han<sup>®</sup> DDD, Coding pin</p>  <p>Only for crimp termination With loss of one contact</p>			09 33 000 9915	