

Number of contacts

5

20 A 500 V 6 kV 3

Yellowlock

Identification	Conductor cross-section (mm ²)	Part number Male	Drawing (dimensions in mm)																		
Han- <i>Yellowlock</i> [®] , Module, Crimp termination, Contact surface: Silver plated	0.14 ... 4 0.14 ... 4 0.14 ... 4	11 05 105 3001 11 05 105 3011 11 05 105 3012	 11 05 105 3001 Grey 11 05 105 3011 Blue 11 05 105 3012 Red																		
Han- <i>Yellowlock</i> [®] , Crimp contact, Contact surface: Silver plated	0.14 ... 0.37 0.5 0.75 1 1.5 2.5 3 4	11 05 000 6101 11 05 000 6102 11 05 000 6103 11 05 000 6104 11 05 000 6105 11 05 000 6106 11 05 000 6107 11 05 000 6108																			
Han- <i>Yellowlock</i> [®] , Crimp contact, Contact surface: Gold plated	0.14 ... 0.37 0.5 0.75 1 1.5 2.5 3 4	11 05 000 6121 11 05 000 6122 11 05 000 6123 11 05 000 6124 11 05 000 6125 11 05 000 6126 11 05 000 6127 11 05 000 6128	<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm² AWG 26-22</td> <td>6.5 mm</td> </tr> <tr> <td>0.5 mm² AWG 20</td> <td>6.5 mm</td> </tr> <tr> <td>0.75 mm² AWG 18</td> <td>6.5 mm</td> </tr> <tr> <td>1 mm² AWG 18</td> <td>6.5 mm</td> </tr> <tr> <td>1.5 mm² AWG 16</td> <td>6.5 mm</td> </tr> <tr> <td>2.5 mm² AWG 14</td> <td>6.5 mm</td> </tr> <tr> <td>3 mm² AWG 12</td> <td>6.5 mm</td> </tr> <tr> <td>4 mm² AWG 12</td> <td>6.5 mm</td> </tr> </tbody> </table> Removal tool 09 99 000 0319 See chapter Han 90	Conductor cross-section	Stripping length	0.14-0.37 mm ² AWG 26-22	6.5 mm	0.5 mm ² AWG 20	6.5 mm	0.75 mm ² AWG 18	6.5 mm	1 mm ² AWG 18	6.5 mm	1.5 mm ² AWG 16	6.5 mm	2.5 mm ² AWG 14	6.5 mm	3 mm ² AWG 12	6.5 mm	4 mm ² AWG 12	6.5 mm
Conductor cross-section	Stripping length																				
0.14-0.37 mm ² AWG 26-22	6.5 mm																				
0.5 mm ² AWG 20	6.5 mm																				
0.75 mm ² AWG 18	6.5 mm																				
1 mm ² AWG 18	6.5 mm																				
1.5 mm ² AWG 16	6.5 mm																				
2.5 mm ² AWG 14	6.5 mm																				
3 mm ² AWG 12	6.5 mm																				
4 mm ² AWG 12	6.5 mm																				