## Han® PushPull L Power 4/0 Metal



Han<sup>®</sup> PushPull L Power 4/0 Genderchanger Metal Han<sup>®</sup> PushPull L Power 4/0 H-distributor Metal

## Features

- High degree of protection IP65 / IP67
- Robust metal housing
- Standard PROFINET component of the German automotive production
- Allows usage of different cable types (Type B,C) e.g. in robots application
- Extension of cords according to PROFINET guideline
- 4-way-distribution of power signals

## **Technical characteristics**

Connector Locking Electrical transmission Number of contacts Mating cycles Housing material Dimensions Degree of protection acc. to DIN 60 529 Mounting

Temperature range Maximum permissible humidity Han® PushPull L Power 4/0 PushPull technology 16 A / 24 V 5 min. 500 Aluminium anodized 83.4 x 62 x 40.7 mm (unmated)

IP65 / IP67 (mated) Wall mountable with 4 screws (type M5) -20 °C ... +50 °C 30 % ... 95 % (no condensation)

