

Number of contacts

9–37



SMT stamped solder pins, straight without grounding pins

| Identification                                                                                   | No. of contacts     | Part number                                                                              |                                                                                          |
|--------------------------------------------------------------------------------------------------|---------------------|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
| <b>Performance levels</b><br>Explanations see page 05.184<br>Other performance levels on request |                     | Performance level 3                                                                      | Performance level 2                                                                      |
| <b>Male connector</b><br>metal shell with dimples                                                | 9<br>15<br>25<br>37 | 09 55 129 78 .. 741<br>09 55 229 78 .. 741<br>09 55 329 78 .. 741<br>09 55 429 78 .. 741 | 09 55 129 68 .. 741<br>09 55 229 68 .. 741<br>09 55 329 68 .. 741<br>09 55 429 68 .. 741 |
| <b>Female connector</b><br>metal shell                                                           | 9<br>15<br>25<br>37 | 09 55 115 76 .. 741<br>09 55 215 76 .. 741<br>09 55 315 76 .. 741<br>09 55 415 76 .. 741 | 09 55 115 66 .. 741<br>09 55 215 66 .. 741<br>09 55 315 66 .. 741<br>09 55 415 66 .. 741 |
| <b>Packaging: 140 pieces on a reel</b>                                                           |                     |                                                                                          |                                                                                          |
| Please insert digit for flange thread or fitted female screw locks                               |                     |                                                                                          |                                                                                          |
| M3 ▶ 11<br>4-40 UNC ▶ 12<br>fixed screw locks M3 ▶ 21<br>fixed screw locks 4-40 UNC ▶ 22         |                     |                                                                                          |                                                                                          |

## Samples

|                                                                       |                     |                                                                                            |                     |
|-----------------------------------------------------------------------|---------------------|--------------------------------------------------------------------------------------------|---------------------|
| Male connector<br>metal shell with dimples                            | 9                   | If performance level 3<br>is required<br>please order as substitute<br>performance level 2 | 09 55 129 68 .. 333 |
|                                                                       | 15                  |                                                                                            | 09 55 229 68 .. 333 |
| 25                                                                    | 09 55 329 68 .. 333 |                                                                                            |                     |
| 37                                                                    | 09 55 429 68 .. 333 |                                                                                            |                     |
| Female connector<br>metal shell                                       | 9                   |                                                                                            | 09 55 115 66 .. 333 |
|                                                                       | 15                  |                                                                                            | 09 55 215 66 .. 333 |
|                                                                       | 25                  |                                                                                            | 09 55 315 66 .. 333 |
|                                                                       | 37                  |                                                                                            | 09 55 415 66 .. 333 |
| Packaging<br>9, 15 contacts: 5 samples<br>25, 37 contacts: 3 samples  |                     |                                                                                            |                     |
| Please insert digit for flange thread<br>or fitted female screw locks |                     |                                                                                            |                     |
| 4-40 UNC ▶ 12                                                         |                     |                                                                                            |                     |
| fixed screw locks 4-40 UNC ▶ 22                                       |                     |                                                                                            |                     |