



Female connectors, straight, THR

Identification	No. of contacts	Part number	Dimensions in mm					
			A	B	C	D	E	G
Female connector, straight, THR stacking heights 6.25 / 9.05 / 13.65 mm	6	15 2 . 006 2401 ...	2.54	6.96	8.89	5.56	4.56	1.19
	8	15 2 . 008 2401 ...	3.81	8.23	10.16	6.83	5.83	1.19
	10	15 2 . 010 2401 ...	5.08	9.50	11.43	8.10	7.10	2.46
	12	15 2 . 012 2401 ...	6.35	10.77	12.70	9.37	8.37	2.46
	14	15 2 . 014 2401 ...	7.62	12.04	13.97	10.64	9.64	3.73
	16	15 2 . 016 2401 ...	8.89	13.31	15.24	11.91	10.91	3.73
	18	15 2 . 018 2401 ...	10.16	14.58	16.51	13.18	12.18	5.00
	20	15 2 . 020 2401 ...	11.43	15.85	17.78	14.45	13.45	5.00
	22	15 2 . 022 2401 ...	12.70	17.12	19.05	15.72	14.72	6.27
	24	15 2 . 024 2401 ...	13.97	18.39	20.32	16.99	15.99	6.27
	26	15 2 . 026 2401 ...	15.24	19.66	21.59	18.26	17.26	7.54
	28	15 2 . 028 2401 ...	16.51	20.93	22.86	19.53	18.53	7.54
	30	15 2 . 030 2401 ...	17.78	22.20	24.13	20.80	19.80	8.81
	32	15 2 . 032 2401 ...	19.05	23.47	25.40	22.07	21.07	8.81
	34	15 2 . 034 2401 ...	20.32	24.74	26.67	23.34	22.34	10.08
	36	15 2 . 036 2401 ...	21.59	26.01	27.94	24.61	23.61	10.08
	38	15 2 . 038 2401 ...	22.86	27.28	29.21	25.88	24.88	11.35
	40	15 2 . 040 2401 ...	24.13	28.55	30.48	27.15	26.15	11.35
	42	15 2 . 042 2401 ...	25.40	29.82	31.75	28.42	27.42	12.62
	44	15 2 . 044 2401 ...	26.67	31.09	33.02	29.69	28.69	12.62
	46	15 2 . 046 2401 ...	27.94	32.36	34.29	30.96	29.96	13.89
	48	15 2 . 048 2401 ...	29.21	33.63	35.56	32.23	31.23	13.89
	50	15 2 . 050 2401 ...	30.48	34.90	36.83	33.50	32.50	15.16
	52	15 2 . 052 2401 ...	31.75	36.17	38.10	34.77	33.77	15.16
	54	15 2 . 054 2401 ...	33.02	37.44	39.37	36.04	35.04	16.43
	56	15 2 . 056 2401 ...	34.29	38.71	40.64	37.31	36.31	16.43
	58	15 2 . 058 2401 ...	35.56	39.98	41.91	38.58	37.58	17.70
	60	15 2 . 060 2401 ...	36.83	41.25	43.18	39.85	38.85	17.70
	62	15 2 . 062 2401 ...	38.10	42.52	44.45	41.12	40.12	18.97
	64	15 2 . 064 2401 ...	39.37	43.79	45.72	42.39	41.39	18.97
	66	15 2 . 066 2401 ...	40.64	45.06	46.99	43.66	42.66	20.24
	68	15 2 . 068 2401 ...	41.91	46.33	48.26	44.93	43.93	20.24
	70	15 2 . 070 2401 ...	43.18	47.60	49.53	46.20	45.20	21.51
	72	15 2 . 072 2401 ...	44.45	48.87	50.80	47.47	46.47	21.51
	74	15 2 . 074 2401 ...	45.72	50.14	52.07	48.74	47.74	22.78
	76	15 2 . 076 2401 ...	46.99	51.41	53.34	50.01	49.01	22.78
	78	15 2 . 078 2401 ...	48.26	52.68	54.61	51.28	50.28	24.05
	80	15 2 . 080 2401 ...	49.53	53.95	55.88	52.55	51.55	24.05
	82	15 2 . 082 2401 ...	50.80	55.22	57.15	53.82	52.82	25.32
	84	15 2 . 084 2401 ...	52.07	56.49	58.42	55.09	54.09	25.32
	86	15 2 . 086 2401 ...	53.34	57.76	59.69	56.36	55.36	26.59
	88	15 2 . 088 2401 ...	54.61	59.03	60.96	57.63	56.63	26.59
	90	15 2 . 090 2401 ...	55.88	60.30	62.23	58.90	57.90	27.86
	92	15 2 . 092 2401 ...	57.15	61.57	63.50	60.17	59.17	27.86
	94	15 2 . 094 2401 ...	58.42	62.84	64.77	61.44	60.44	29.13
	96	15 2 . 096 2401 ...	59.69	64.11	66.04	62.71	61.71	29.13
	98	15 2 . 098 2401 ...	60.96	65.38	67.31	63.98	62.98	30.40
	100	15 2 . 100 2401 ...	62.23	66.65	68.58	65.25	64.25	30.40

Please insert digit for stacking height

- 6.25 mm ► 1
- 9.05 mm ► 2
- 13.65 mm ► 3