Ha-VIS mCon 3000

Ethernet Switch Ha-VIS mCon 3100-AV 10-port Ethernet Switch for mounting onto top-hat mounting rail in control cabinets									
Managed	IP30		PROFINET compatible		le X	EtherNet/IP compatible \overline{X}		XI	
Number of ports, Copper / Termination		10x 10/	10x 10/100Base-T(X) / RJ45 (Twisted Pair)						
Input voltage / Termination Permissible range (min./r Input current Alarm signalling contact Housing material Dimensions (W x H x D) Weight Working temperature Approvals MTBF Management		for redu 9.6 V approx. Change 3-pole p metal, p 60 x 13 approx. -40 °C . UL 508 625.000 fully ma	indant p . 60 V D . 190 mA e-over co bluggabl bowder-o 2 x 104 0.6 kg +70 °(; UL 60 s 0 h inaged v	(at 24 V DC) ontact, potentia e screw contac coated mm (including	ll-free, 24 v ct cap, witho ce and SN	V DC / 0.5 A ut connecto			
Identification	Pa	art number	Dra	wing			Dimension	s in mm	
Ha-VIS mCon 3100-AV Ethernet Switch with 10 RJ45 ports including set for assembly on stand		76 110 400:							

Ha-VIS mCon