

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)	
Han-Eco® Modular, Surface mounted housing, With integrated cable gland, Side entry, IP65	1x M32 2x M32	13 21 13 21	19 41 110 0232 19 41 110 0272	11, 2 - 11, 2 - 11, 2 - 12, 2	Han Eco
				87 — 99 — 37,4 — 68 —	
Han-Eco® Modular, Cable to cable housing, With integrated cable gland, Top entry, IP65	1x M32	13 21	19 41 110 0722	SW36 1 9 9 13-21 - 24 - 24 - 24 - 24 - 24 - 24 - 24 -	
Han-Eco® Modular, Protection cover, for hoods, IP65			19 41 010 5406	79 Hen-Ecs 106 184H95458 SR 58,25	
Han-Eco® Modular, Protection cover, for hoods, With fixing cord (loop), IP65			19 41 010 5407	79 100 100 100 100 100 100 100 10	
Han-Eco® Modular, Protection cover, for bulkhead mounted housings, for surface mounted housings, for cable to cable housing, With fixing cord (loop), IP65			19 41 010 5402	8 8 9 9 2 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	L on
					Han 29 17