Han[®] Hood Link

HARTING

Features	Technical characteristics
 Cable to cable connection simple to realise and easy to mount Resistant elastomer Locking as well as seal combined in one system for two lever locking system 	Limiting temperature-40 +85 °CDegree of protection acc. to IECIP65, locked condition60529Colour (hood/housing)BlackRoHScompliant
Identification	Drawing Part number (dimensions in mm)
Tocking element, for hoods, iP65 locked condition	