



Ha-VIS preLink® Han® PushPull Metal Outlet and Han® 3 A Metal Outlet

Advantages

- Simple mounting, fixing and earth connection both outside
- Fast termination of data cables due to Ha-VIS preLink® technology
- Structured cabling for industrial premises
- Mating face AIDA compliant, protection cover incl.
- PROFINET compatible

Technical characteristics

| | |
|---------------------------------------|--|
| Number of ports, Copper / Termination | 2 x Han® PushPull RJ45 (IP65 / IP67) or Han® 3 A RJ45 |
| Transmission performance | Category 6 / Class E _A up to 500 MHz acc. to ISO/IEC 11 801:2002, EN 50 173-1 |
| Transmission rate | up to 10 Gbit/s |
| Termination | Ha-VIS preLink® |
| Wire gauge | AWG 24 ... 22 (0.25 mm ² ... 0.34 mm ²) solid and stranded |
| Strand diameter | Ø 1.3 mm ... 1.6 mm |
| Cable diameter | 7.2 mm ... 8 mm |
| Shielding | Fully shielded 360° flexible shielding termination |
| Mounting | Wall mounting |
| Dimensions (H x W x D) | 105 x 105 x 40.5 mm |
| Degree of protection | IP65 / IP67 |
| Operating temperature range | -40 °C ... +70 °C |
| Housing material | Aluminium, die-cast |
| Colour | Black |

| Identification | Part number | Drawing | Dimensions in mm |
|---|----------------|---------|------------------|
| Ha-VIS preLink® Han® PushPull Metal Outlet consists of: <ul style="list-style-type: none"> • 1x Housing including protection covers • 2x Ha-VIS preLink® Set RJ45 jack AWG 22/23 • 2x Cable gland with slotted seal • 1x Assembly instruction | 20 82 104 0101 | | |
| Ha-VIS preLink® Han® 3 A Metal Outlet consists of: <ul style="list-style-type: none"> • 1x Housing including protection covers • 2x Ha-VIS preLink® Set RJ45 jack AWG 22/23 • 2x Cable gland with slotted seal • 1x Assembly instruction | 20 82 102 0101 | | |