



Han E/EE

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® ESS, Cage-clamp termination, Contact surface: Silver plated</p>  <p>two terminations per contact for hoods/housings high construction only</p>	0.14 ... 2.5	09 33 006 2672	09 33 006 2772	 <p>1) distance for contact max. 21 mm</p> <p>Contact arrangement (view from termination side)</p> <p>Panel cut out</p>