





Han E/EE

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® ES Press, Cage-clamp termination, 1 ... 16</p> <p>Contact surface: Silver plated</p>  <p>Blue slide for hoods/housings high construction only You need two inserts for a complete assembly!</p>	0.14 ... 2.5	09 33 016 2648	09 33 016 2748	 <p>Distance for contact max. 21 mm</p>
<p>Han® ES Press, Continuing marking, Cage-clamp termination, 17 ... 32</p> <p>Contact surface: Silver plated</p>  <p>Blue slide for hoods/housings high construction only You need two inserts for a complete assembly!</p>	0.14 ... 2.5	09 33 016 2688	09 33 016 2788	 <p>Panel cut out</p>