










Special hoods/housings for Han Hv E® screw terminal
Double locking lever

Han
Hv E

Identification	Cable entry	Part number Low construction	Drawing (dimensions in mm)
Han Hv E®, Hood, Top entry, IP65 	1x M20 1x M25	19 34 003 0420 19 34 003 0421	
Han Hv E®, Hood, Side entry, IP65 	1x M20	19 34 003 0520	
Han Hv E®, Bulkhead mounted housing, Han-Easy Lock®, IP65 		09 34 003 0301	 <p>Panel cut out 60 x 35 mm</p>
Han Hv E®, Surface mounted housing, Side entry, Han-Easy Lock®, IP65 	2x M20	19 34 003 0270	
Han Hv E®, Cable to cable housing, Top entry, Han-Easy Lock®, IP65 	1x M20 1x M25	19 34 003 0730 19 34 003 0731	