










Special hoods/housings for Han Hv E® screw terminal
Double locking lever

Han
Hv E

Identification	Cable entry	Part number Low construction	Drawing (dimensions in mm)
Han Hv E®, Hood, Top entry, IP65 	1x M32	19 34 010 0422	
Han Hv E®, Hood, Side entry, IP65 	1x M25	19 34 010 0521	
Han Hv E®, Bulkhead mounted housing, Han-Easy Lock®, IP65 		09 34 010 0301	 <p>Panel cut out 108 x 35 mm</p>
Han Hv E®, Surface mounted housing, Side entry, Han-Easy Lock®, IP65 	2x M25	19 34 010 0271	
Han Hv E®, Cable to cable housing, Top entry, Han-Easy Lock®, IP65 	1x M32	19 34 010 0732	