




Number of contacts

4+

80 A 830 V 8 kV 3

Han-Com

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																							
		Male	Female																								
Han-Com®, Han® K 4/0, Screw termination, Contact surface: Silver plated 	1.5 ... 16	09 38 006 2611	09 38 006 2711	 <p>1) distance for contact max. 21 mm</p>  <p>1 3 2 4 (M) 3 1 4 2 (F)</p> <p>Contact arrangement (view from termination side)</p> <table border="1"> <thead> <tr> <th rowspan="2">Conductor cross-section</th> <th colspan="2">Power contacts</th> </tr> <tr> <th>Tightening torque</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>1.2 Nm</td> <td>14 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>2 Nm</td> <td>14 mm</td> </tr> <tr> <td>4 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>6 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>10 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> <tr> <td>16 mm²</td> <td>3 Nm</td> <td>14 mm</td> </tr> </tbody> </table>	Conductor cross-section	Power contacts		Tightening torque	Stripping length	1.5 mm ²	1.2 Nm	14 mm	2.5 mm ²	2 Nm	14 mm	4 mm ²	3 Nm	14 mm	6 mm ²	3 Nm	14 mm	10 mm ²	3 Nm	14 mm	16 mm ²	3 Nm	14 mm
Conductor cross-section	Power contacts																										
	Tightening torque	Stripping length																									
1.5 mm ²	1.2 Nm	14 mm																									
2.5 mm ²	2 Nm	14 mm																									
4 mm ²	3 Nm	14 mm																									
6 mm ²	3 Nm	14 mm																									
10 mm ²	3 Nm	14 mm																									
16 mm ²	3 Nm	14 mm																									