







Number of contacts

8

5 A 50 V 0.8 kV 3
+ shielding

Modular

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han-Modular®, Adapter module, Han® Gigabit module, Han® Shielded module, Han® Megabit module</p> 		09 14 001 3011	09 14 001 3111	
<p>Han® Gigabit insert, Crimp termination, Cat. 7_A</p>  <p>Please order crimp contacts separately. Please order adapter module separately.</p>	0.09 ... 0.52	09 14 008 3031	09 14 008 3131	 <p>Cable outer diameter ≤ 14 mm</p>
<p>Han® Gigabit insert, Crimp termination, Cat. 7_A</p>  <p>With additional shield connection to the hinged frame Please order crimp contacts separately. Please order adapter module separately.</p>	0.09 ... 0.52	09 14 008 3032	09 14 008 3132	 <p>Cable outer diameter ≤ 14 mm</p>