

Modular

Identification	Part number		Drawing (dimensions in mm)																																																							
	Male	Female																																																								
DIN 41626, Coaxial contact, Solder/crimp termination, for cables RG 174 U, 188 AU, 316 U, 50 Ohm, Contact surface: Gold plated	09 14 000 6211	09 14 000 6111																																																								
DIN 41626, Coaxial contact, Solder/crimp termination, for cables RG 179 BU, 187 AU, 75 Ohm, Contact surface: Gold plated	09 14 000 6221	09 14 000 6121																																																								
			<table border="1"> <thead> <tr> <th rowspan="2">Wires</th> <th>Shell</th> <th>Internal wire</th> <th colspan="3">Dämpfung db/100 m bei</th> </tr> <tr> <th>∅ mm</th> <th>∅ mm</th> <th>100MHz</th> <th>200MHz</th> <th>800MHz</th> </tr> </thead> <tbody> <tr> <td>50 Ω</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>RG 174 / U</td> <td>2.5</td> <td>0.48</td> <td></td> <td></td> <td>84</td> </tr> <tr> <td>RG 188 A / U</td> <td>2.6</td> <td>0.54</td> <td>29</td> <td>40</td> <td></td> </tr> <tr> <td>RG 316 / U</td> <td>2.5</td> <td>0.54</td> <td></td> <td>40</td> <td></td> </tr> <tr> <td>75 Ω</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>RG 179 B / U</td> <td>2.55</td> <td>0.3</td> <td></td> <td>41</td> <td></td> </tr> <tr> <td>RG 187 A / U</td> <td>2.7</td> <td>0.3</td> <td></td> <td>41</td> <td></td> </tr> </tbody> </table>			Wires	Shell	Internal wire	Dämpfung db/100 m bei			∅ mm	∅ mm	100MHz	200MHz	800MHz	50 Ω						RG 174 / U	2.5	0.48			84	RG 188 A / U	2.6	0.54	29	40		RG 316 / U	2.5	0.54		40		75 Ω						RG 179 B / U	2.55	0.3		41		RG 187 A / U	2.7	0.3		41	
Wires	Shell	Internal wire	Dämpfung db/100 m bei																																																							
	∅ mm	∅ mm	100MHz	200MHz	800MHz																																																					
50 Ω																																																										
RG 174 / U	2.5	0.48			84																																																					
RG 188 A / U	2.6	0.54	29	40																																																						
RG 316 / U	2.5	0.54		40																																																						
75 Ω																																																										
RG 179 B / U	2.55	0.3		41																																																						
RG 187 A / U	2.7	0.3		41																																																						
DIN 41626, FO contact, for 1 mm plastic fibre	20 10 001 4211	20 10 001 4221																																																								
DIN 41626, FO contact, for SI fibre (HCS®) 200/230 µm	20 10 230 4211	20 10 230 4221																																																								
DIN 41626, FO contact, for GI fibre 50/125 µm, for ceramic ferrule 62.5/125 µm	20 10 125 4212	20 10 125 4222																																																								