









Number of contacts

# 17

10 A 160 V 2.5 kV 3

Modular

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																					
		Male	Female																						
Han-Modular®, Han® DDD module, Crimp termination  <p>Please order crimp contacts separately.</p>	0.14 ... 2.5	09 14 017 3001	09 14 017 3101	 <p>Contact arrangement (view from termination side)</p>																					
Han D®, Crimp contact, Contact surface: Silver plated 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5	09 15 000 6104 09 15 000 6103 09 15 000 6105 09 15 000 6102 09 15 000 6101 09 15 000 6106	09 15 000 6204 09 15 000 6203 09 15 000 6205 09 15 000 6202 09 15 000 6201 09 15 000 6206	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup> AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup> AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup> AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup> AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section	∅	Stripping length	0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm
Conductor cross-section	∅	Stripping length																							
0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm																							
0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm																							
0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm																							
1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm																							
1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm																							
2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm																							
Han D®, Crimp contact, Contact surface: Gold plated 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5	09 15 000 6124 09 15 000 6123 09 15 000 6125 09 15 000 6122 09 15 000 6121 09 15 000 6126	09 15 000 6224 09 15 000 6223 09 15 000 6225 09 15 000 6222 09 15 000 6221 09 15 000 6226	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup> AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup> AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup> AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup> AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section	∅	Stripping length	0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm
Conductor cross-section	∅	Stripping length																							
0.14-0.37 mm <sup>2</sup> AWG 26-22	0.9 mm	8 mm																							
0.5 mm <sup>2</sup> AWG 20	1.1 mm	8 mm																							
0.75 mm <sup>2</sup> AWG 18	1.3 mm	8 mm																							
1 mm <sup>2</sup> AWG 18	1.45 mm	8 mm																							
1.5 mm <sup>2</sup> AWG 16	1.75 mm	8 mm																							
2.5 mm <sup>2</sup> AWG 14	2.25 mm	6 mm																							
FO contact, for 1 mm plastic fibre 		20 10 001 3211	20 10 001 3221	 <p>20 10 001 3211 + 20 10 001 3221</p>																					