

Number of contacts

# 24+

16 A 500 V 6 kV 3

Han  
AV

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han E<sup>®</sup> AV, Terminal block connector, Left hand version, Multi contour (MK), Screw termination, Contact surface: Silver plated</p>	0.2 ... 2.5	09 33 024 4625	09 33 024 4725	
<p>Han E<sup>®</sup> AV, Terminal block connector, Left hand version, Single contour (SK), Screw termination, Contact surface: Silver plated</p>	0.2 ... 2.5	09 33 024 4626	09 33 024 4726	
<p>Han E<sup>®</sup> AV, Terminal block connector, Left hand version, Single contour (SK), Screw termination, Contact surface: Silver plated</p>	0.2 ... 2.5	09 33 024 4626	09 33 024 4726	