









Number of contacts

16+

16 A 500 V 6 kV 3

Han AV

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)	
		Male	Female		
Han® ES AV, Terminal block connector, Left hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated 	0.14 ... 2.5	09 33 016 4629	09 33 016 4729		
					
					
Han® ES AV, Terminal block connector, Right hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated 	0.14 ... 2.5	09 33 016 4639	09 33 016 4739	