

Number of contacts

24+

16 A 500 V 6 kV 3

Han
AV

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® ES AV, Terminal block connector, Left hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated</p>	0.14 ... 2.5	09 33 024 4629	09 33 024 4729	
<p>Han® ES AV, Terminal block connector, Right hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated</p>	0.14 ... 2.5	09 33 024 4639	09 33 024 4739	