






Technical characteristics

Limiting temperature -40 ... +100 °C
 Degree of protection acc. to IEC IP65
 60529

Technical characteristics

Material (cable glands) Thermoplastic
 Colour (accessories) Black
 RoHS compliant, compliant with exemption

Identification	Size	Clamping range (mm)	Part number	Drawing (dimensions in mm)
Han-Compact®, Cable gland, for hoods, for cable to cable housing, Pg 16, IP65 	Pg 16 Pg 16 Pg 16	6.5 ... 9.5 9 ... 13 11.5 ... 15.5	09 00 000 5047 09 00 000 5156 09 00 000 5059	SW27 
Han-Compact®, Cable gland, for surface mounted housings, Pg 16, IP65 	Pg 16 Pg 16	6.5 ... 9.5 11.5 ... 15.5	09 00 000 5057 09 00 000 5058	SW27 
Han-Compact®, Cable gland, for hoods, for cable to cable housing, Pg 21, IP65 	Pg 21 Pg 21	14 ... 18 17 ... 20.5	09 00 000 5157 09 00 000 5158	SW33 