




Number of contacts

# 2+

40 A 830 V 6 kV 3

Han Q

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han <sup>®</sup> Q, 2/0 High Voltage, Axial screw termination, Pack contents: With heat shrink tube Contact surface: Silver plated 	1.5 ... 2.5 2.5 ... 6 4 ... 10	09 12 002 2656 09 12 002 2654 09 12 002 2652	09 12 002 2756 09 12 002 2754 09 12 002 2752	 <p>Stripping length 8 ... 9 mm                      Tightening torque 1.8 Nm</p>
Coding element 		09 12 000 9922		