









Hoods/housings for harsh outdoor environments
Screw locking

Han
HC

Identification	Cable entry	Part number	Drawing (dimensions in mm)
<p>Han® HPR, Hood, Enlarged, Top entry, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p> 	4x M25	19 40 024 0478	
<p>Han® HPR, Bulkhead mounted housing, Enlarged, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p> 		09 40 024 0368	
<p>Han® HPR, Surface mounted housing, Horizontal version, Enlarged, Top entry, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p>  <p>Bulkhead mounted housing 09 40 024 0368 not included, please order separately</p>	4x M25	19 40 024 0978	
<p>Mounting frames, Han® HPR, Thread M6</p> 		09 40 000 9904	 <p>Panel cut out</p>