





Hoods/housings for rough environments
Single locking lever

Han
HC

Identification	Part number Low construction	Drawing (dimensions in mm)
<p>Han® M, Bulkhead mounted housing, With thermo-plastic cover, IP65</p> 	<p>09 37 048 0301</p>	
<p>Han® M, Frame, for male inserts, for female inserts, 4x HC 350 contacts + 2x Han® Q 5/0 in a bulkhead mounted housing</p> 	<p>09 11 000 9955</p>	 <p>Tightening torque Fixing screws M3: 0.5 Nm Tightening torque Fixing screws Han® Q 5/0: 0.25 Nm Tightening torque Cross-tying screws 1.5 Nm</p>