






Hoods/housings for harsh outdoor environments
Screw locking

Han
HC

Identification	Cable entry	Conductor cross-section (mm ²)	Part number	Drawing (dimensions in mm)
<p>Han® HPR EasyCon, Hood, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p> 			09 40 024 0451	 <p>Tightening torque Cover locking 6 Nm Tightening torque External PE 15 Nm</p>
<p>Han® HPR EasyCon, Surface mounted housing, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p> 			09 40 024 0951	 <p>Tightening torque Cover locking 6 Nm Tightening torque External PE 15 Nm</p>
<p>Han® HPR EasyCon, Mounting cover, for surface mounted housings, for hoods, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p> 	3x M25 3x M32 4x M25		19 40 024 9901 19 40 024 9903 19 40 024 9902	