









Hoods/housings for harsh outdoor environments
Screw locking

Han
HC

| Identification | Cable entry | Part number | Drawing (dimensions in mm) |
|---|----------------------------------|--|--|
| <p>Han® HPR, Hood, Special type, Top entry, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p>  | <p>1x M63</p> | <p>19 40 024 0420</p> |  |
| <p>Han® HPR, Hood, Top entry, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p>  | <p>3x M25 3x M25, 1x M20</p> | <p>19 40 024 0461 19 40 024 0471</p> |  |
| <p>Han® HPR, Hood, Special type, Angled entry, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p>  | <p>3x M25</p> | <p>19 40 024 0631</p> |  |
| <p>Han® HPR, Bulkhead mounted housing, IP65, IP68, IP69 / IPX9K acc. to ISO 20653</p>  | | <p>09 40 024 0311</p> |  |