

Number of contacts

2

10 A 50 V 0.8 kV 3
+ 4 electrical contacts 10 A + option for PE



Han-Brid

Identification	Part number		Drawing (dimensions in mm)
	Male	Female	
Han-Brid®, Han-Brid® FO, Hybrid field bus connector Device side FO (f) + Han D® (m) With PCB	09 12 004 2611		<p>Contact arrangement (view from termination side) Also available as single parts: 09 12 004 3011 Lower part, unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector Cable side FO (m) + Han D® (f) for POF		09 12 004 2711	<p>09 12 004 3111 Unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector Cable side FO (m) + Han D® (f) for POF crimpless		09 12 004 2713	<p>09 12 004 3113 Unloaded</p>
Han-Brid®, Han-Brid® FO, Hybrid field bus connector Cable side FO (m) + Han D® (f) for HCS® fibre		09 12 004 2716	<p>09 12 004 3116 Unloaded</p>