

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																												
		Male	Female																													
Han D®, Crimp contact, Contact surface: Gold plated	0.14 ... 0.37	09 15 000 6124	09 15 000 6224																													
	0.5	09 15 000 6123	09 15 000 6223																													
	0.75	09 15 000 6125	09 15 000 6225																													
	1	09 15 000 6122	09 15 000 6222																													
	1.5	09 15 000 6121	09 15 000 6221																													
	2.5	09 15 000 6126	09 15 000 6226																													
				<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th></th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm<sup>2</sup></td> <td>AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm<sup>2</sup></td> <td>AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm<sup>2</sup></td> <td>AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section		∅	Stripping length	0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm	0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm	0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm	1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm	1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm	2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm
Conductor cross-section		∅	Stripping length																													
0.14-0.37 mm <sup>2</sup>	AWG 26-22	0.9 mm	8 mm																													
0.5 mm <sup>2</sup>	AWG 20	1.1 mm	8 mm																													
0.75 mm <sup>2</sup>	AWG 18	1.3 mm	8 mm																													
1 mm <sup>2</sup>	AWG 18	1.45 mm	8 mm																													
1.5 mm <sup>2</sup>	AWG 16	1.75 mm	8 mm																													
2.5 mm <sup>2</sup>	AWG 14	2.25 mm	6 mm																													