






Number of contacts

# 2

10 A 50 V 0.8 kV 3  
+ 4 electrical contacts 10 A + option for PE



Han-Brid

| Identification   | Part number    |                | Drawing<br>(dimensions in mm)   |
|--|----------------|----------------|---|
|  | Male           | Female         |   |
| <p>Han-Brid®,<br/>Han-Brid® Cu,<br/>Hybrid field bus connector</p> <p>Device side</p>   | 09 12 006 2611 |                |   <p>Also available as single parts:<br/>09 12 002 2611 Upper part, loaded<br/>09 12 002 3011 Upper part, unloaded<br/>09 12 004 3011 Lower part, unloaded</p> |
| <p>Han-Brid®,<br/>Han-Brid® Cu,<br/>Hybrid field bus connector</p> <p>Cable side</p>  |                | 09 12 006 3111 |  <p>Contact arrangement (view from termination side)</p>  |