

## Features

- Robust design
- Suitable for standard and EMC hoods and housings
- Low wiring costs
- High density of contacts

## Technical characteristics

Rated current	7.5 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Contact resistance	≤3 mΩ
Limiting temperature	-40 ... +125 °C
Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
RoHS	compliant with exemption

## Specifications and approvals

EN 60664-1  
 IEC 61984  
 UL 1977 ECBT2.E235076  
 CSA-C22.2 No. 182.3 ECBT8.E235076

## Details

**Han DD® crimp inserts** see chapter Han 02

**Modules** see chapter Han 06

**Han® B bulkhead mounted housings** see chapter Han 31

**Crimping tools** see chapter Han 90