









Hoods/housings for rough environments  
Single locking lever

Identification	Cable entry	Part number		Drawing (dimensions in mm)
		Low construction	High construction	
Han® M, Hood, Top entry, IP65, IP66, IP67  	2x M32		19 37 024 0457	
Han® M, Hood, Side entry, IP65, IP66, IP67  	1x M40		19 37 024 0548	
Han® M, Bulkhead mounted housing, Rear mounting, IP66  Pack contents: Mounting frame is included with- in the delivery  		09 37 024 0397		 <p>Panel cut out</p>
Han® M, Bulkhead mounted housing, Rear mounting, IP66  		09 37 024 0398		 <p>Panel cut out</p>