





Number of contacts

16+

16 A 250 V 4 kV 3

Ther-
mo

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han® Thermocouple, Han A®, Screw termination 	1 ... 2.5	09 20 016 2691	09 20 016 2891	 <p>1) Distance for contact max. 24 mm Stripping length 7.5 mm Tightening torque 0.5 Nm</p>  <ul style="list-style-type: none"> ◆ Fe ○ CuNi  <p>Panel cut out for use without Hoods/Housings</p>