







Number of contacts

24+

16 A 400 V 6 kV 3

Ther-
mo

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han[®] Thermocouple, Han E[®], Screw termination, With wire protection</p>  <p>Also suitable for standard contacts</p>	1 ... 2.5	09 33 024 2689	09 33 024 2789	 <p>1) distance for contact max. 21 mm</p>  <p>Standard contacts ◆ Fe ○ CuNi</p>
<p>Han[®] Thermocouple, Han E[®], Screw termination, With wire protection</p> 	1 ... 2.5	09 33 024 2691	09 33 024 2791	 <p>◆ Fe ○ CuNi</p>  <p>Panel cut out</p>