







Number of contacts

24+

16 A 500 V 6 kV 3

Han E/EE

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han® ES, Cage-clamp termination, Contact surface: Silver plated 	0.14 ... 2.5	09 33 024 2616	09 33 024 2716	 <p>1) distance for contact max. 21 mm</p>
Han® ES Press, Cage-clamp termination, Contact surface: Silver plated  <p>Blue slide                      for hoods/housings high construction only</p>	0.14 ... 2.5	09 33 024 2648	09 33 024 2748	 <p>Distance for contact max. 21 mm</p>  <p>Contact arrangement (view from termination side)</p>  <p>Panel cut out</p>